

UNI-MDPDH180

Pendant Mount Adaptor for outdoor Minidome Cameras



Overview

The UNI-MDPDH180 is a 1-inch thread pendant adaptor for use with Sony SNC-VM632R/VM602R/EM632RC/EM602RC and SNC-DH160/DH180/DH260/DH280 video security cameras.

1" NPT pipe thread for pendant mounting. Also suitable for wall mounting (with UNI-WMB4 gooseneck wall mount bracket).

Kit includes gaskets and Teflon tape for water ingress protection outdoors.

All aluminium construction. Light grey finish. Suitable for outdoor or indoor use.

Technical Specifications

Architecture / Engineering Specifications		
<ul style="list-style-type: none">Size (H x W x D)	6.8 x 6.8 x 3.4 inches (173 x 173 x 86.4 mm)	
<ul style="list-style-type: none">Weight	0.9 lbs. (0.44 kg)	
<ul style="list-style-type: none">Body Construction	Aluminum	
Shipping		
<ul style="list-style-type: none">Weight	1.35 lbs. (0.6 kg)	
<ul style="list-style-type: none">Dimensions	9 x 8 x 4 inches (229 x 203 x 102 mm)	
Mounting Accessories		
<ul style="list-style-type: none">UNI-CMA1	White aluminum corner mount	
<ul style="list-style-type: none">UNI-PMA1	White aluminum pole mount	
<ul style="list-style-type: none">UNI-WMBB1	White aluminum wall / pole with (2) 23 inch mounting straps	
<ul style="list-style-type: none">UNI-WMB4	White aluminum wall mount	
Compatible Camera Models		
<ul style="list-style-type: none">SNC-DH160 / SNC-DH180	720p HD, IR Vandal Resistant	
<ul style="list-style-type: none">SNC-DH260 / SNC-DH280	1080p HD, IR Vandal Resistant	
<ul style="list-style-type: none">SNC-EM602RC / SNC-EM632RC	720p/30fps HD, IR Ruggedized E series 1080p/30fps Full HD, IR Ruggedized E series	
<ul style="list-style-type: none">SNC-VM602R / SNC-VM632R	720p/60fps HD, IR Ruggedized V series; 1080p/60fps Full HD, IR Ruggedized V series	