

UNI-WMB4

Gooseneck Wall Mount Bracket



Overview

This Gooseneck Wall Mount Bracket is ideal for outdoor installation of Sony mini dome video security cameras.

The 1" pipe thread is compatible with UNI-MDPHM, UNI-MDPDH180, UNI-MDPH120, UNI-MDPX, and UNI-MDPVM772 pendant mount adaptor.

Standard wall fixing hole pattern is compatible with corner mount adaptor (UNI-CMA1), pole mount adaptor (UNI-PMA1) and outdoor power block case (UNI-PBU1). The pendant mount adaptor is needed when using the UNI-WMB4.

All aluminium construction. Light grey finish. Suitable for outdoor or indoor use.

Using adapters, the following models can be attached to this mount

UNI-MDPDH120

SNC-EM520, SNC-EM521, SNC-DH120, SNC-DH120T, SNC-DH140, SNC-DH140T, SNC-DH220, SNC-DH220T, SNC-DH240, SNC-DH240T, SNC-ZM550, SNC-ZM551, SNC-EM600, SNC-EM630, SNC-VM600B, SNC-VM600, SNC-VM630, SNC-EM601, SNC-EM631, SNC-VM601B, SNC-VM601, SNC-VM631

UNI-MDPX

SNC-DH110T/B, SNC-DH110/W, SNC-DH110/B, SNC-DH110T/W, SNC-DH210T/B, SNC-DH210T/W, SNC-DH210/W, SNC-DH210/B, SNC-XM631

UNI-MDPDH180

SNC-DH160, SNC-DH180, SNC-DH260, SNC-DH280, SNC-EM602R, SNC-EM632R, SNC-VM602R, SNC-VM632R, SNC-EM602RC, SNC-EM632RC

UNI-MDPHM

SNC-HM662

UNI-MDPVM772

SNC-VM772R

Technical Specifications

Architecture / Engineering Specifications	
● Size (H x W x D)	6.4 x 9.8 x 3.3 inches (162 x 249 x 83 mm)
● Weight	1.25 lbs. (.56 kg)
● Body Construction	Aluminum
Attributes	
● Environment	Indoor / Outdoor
● Mounting Style	Wall Gooseneck
● RoHS	Yes
● WEEE	Yes
Shipping	
● Weight	4 lbs. (2 kg)
● Dimensions	9 x 8 x 4 inches (229 x 203 x 102 mm)
Mounting Accessories	
● UNI-CMA1	Corner mount
● UNI-PMA1	Pole mount
● UNI-WMBB1	Wall / Pole mount
Compatible Pendant Shrouds	
● UNI-MDPHM	Camera housing pendant mounting adapter
● UNI-MDPDH180	Camera outdoor pendant mount adapter
● UNI-MDPDH120	Camera housing pendant mounting adapter
● UNI-MDPX	Pendent Mount Adapter for x Series Mini Domes