

Weather Resistant Indoor/Outdoor 3-Way Polypropylene ConeSpeaker System with Dual Built-In Line Transformer

DMS3TS Black housing
DMS3TSW White housing

Features

- 3-way mini weather resistant speaker system
- Dual voltage transformer: 70V and 25V



Specifications

Frequency Response	55Hz – 20kHz
Woofer	4" 10 oz. polypropylene air suspension
Tweeter	1" dome tweeter
Midrange	2"
Voice Coil	50W, 8 Ohms
Rotary Switch	70/25V line or 8 Ohms adjustable
Transformer	15W/330 Ohms, 7.5W/660 Ohms, 4W/1250 Ohms, 2W/2500 Ohms, 1W/5000 Ohms
Dimensions	4.375" (L) x 4.5" (W) x 7.25" (H)
Housing	Die cast enclosure
Included in Box	Mounting bracket, wire & hardware