

5" High Resolution TFT Color LCD Monitor with Remote Control

VM5LCD

Features

Our 5 inch high resolution TFT flat screen LCD monitor offers convenient on-screen display controls located on the front panel; including controls for brightness, contrast, hue, color, vertical/horizontal positioning and volume. It also features audio with front mounted speakers and input signal detection provides for easy connection. 12VDC power supply and A/V cable are included.

- 1 year warranty.



Specifications

Screen Size	5"
Aspect Ratio	4:3
Resolution/Scan	640 x 480
Brightness.....	350 cd/m2
Contrast Ratio.....	250:1
Inputs.....	1 S video, 2 RCA
Audio Input	2 RCA
Power Supply	12VDC (power supply included)
Dimensions.....	6.5" (W) x 4.5 (H)
Weight	1 lb.
Base	2"