

ERWEN-12E

19" Equipment Hinged Wall Rack Enclosure – 12U

Product Features:

Welded steel construction

Ships fully assembled

Works with all standard 19" rack equipment and accessories

Rails have numbered spaces with standard 10-32 threading

Adjustable front and rear rails

Vented top and bottom

Top and bottom cable routing knockouts

Reversible hinged tempered glass front door

Removable, locking side panels

Removable hinged back panel

Load capacity – 120 lbs

Black powder coat finish

Product Specifications:

(for Architects & Engineers)

The 12U (Rack Unit) wall mounted equipment rack enclosure shall be the Video Mount Products (VMP) ERWEN-12E. The overall dimensions for the ERWEN-12E are 25.3" H x 24.3" W x 21.8" D with a maximum useable depth of 16". The ERWEN-12E shall work with all EIA compliant 19" rack equipment and accessories which are less than 16" in depth. The ERWEN-12E shall come equipped with two sets of adjustable rack rails which are #10-32UNF threaded and have rack spaces numbered. The ERWEN-12E shall come with a lockable, reversible tempered glass front door. The ERWEN-12E shall have a removable wall plate with mounting holes for wooden studs with 16" centers. The ERWEN-12E shall have a lockable, hinged wall plate allowing the main enclosure to rotate 90 degrees while mounted on the wall and fully loaded. The ERWEN-12E shall have a vented top and bottom with cable entry and exit points located on the top and bottom of the wall plate and on the top of the main enclosure. The ERWEN-12E shall have two mounting points for standard fans which can be purchased separately. The ERWEN-12E shall have removable, locking side panels (locks included). The ERWEN-12E shall have a load capacity of 120 lbs. The ERWEN-12E shall be fully welded and ship assembled. The ERWEN-12E shall have a powder coat black finish.



Video Mount Products

345 Log Canoe Circle Stevensville, MD 21666

Toll Free: 877.281.2169 Telephone: 410.643.6390

Facsimile: 410.643.6615 www.videomount.com

VMP
VIDEO MOUNT PRODUCTS