



1316MCLICK

Miniature Click-on Hanger for 13–16 mm cable

Dimensions

Nominal Size	1/2 in 3/8 in
Compatible Diameter, maximum	16.256 mm 0.640 in
Compatible Diameter, minimum	13.716 mm 0.540 in
Height	38.00 mm 1.50 in
Length	55.00 mm 2.17 in
Width	25.00 mm 0.98 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

General Specifications

Hanger Type	Click-on hanger
Cables per Hanger	2
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Ordering Note	CommScope® standard product in Europe, the Middle East, and Africa CommScope® standard product in the United States and Canada
Package Quantity	10

Mechanical Specifications

Mounting	M8 through hole
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	=100 hours exposure in accelerated UV life chamber
Vibration Survival	=4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	44.7 cm 17.6 in
Length	17.7 cm 7.0 in
Shipping Weight	0.05 kg 0.12 lb
Width	39.4 cm 15.5 in

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications

COMMScope®

1316MCLICK

RoHS 2011/65/EU

China RoHS SJ/T 11364-2006

ISO 9001:2008

Compliant

Below Maximum Concentration Value (MCV)

Designed, manufactured and/or distributed under this quality management system

