



68MCLICK

Miniature Click-on Hanger for 6–8 mm cable

Dimensions

Nominal Size	1/4 in
Compatible Diameter, maximum	8.128 mm 0.320 in
Compatible Diameter, minimum	5.842 mm 0.230 in
Height	38.00 mm 1.50 in
Length	35.00 mm 1.38 in
Width	16.00 mm 0.63 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

General Specifications

Hanger Type	Click-on hanger
Cables per Hanger	2
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Ordering Note	CommScope® non-standard product
Package Quantity	10

Mechanical Specifications

Mounting	M8 through hole
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	=100 hours exposure in accelerated UV life chamber
Vibration Survival	=4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	30.4 cm 12.0 in
Length	2.5 cm 1.0 in
Shipping Weight	0.09 kg 0.20 lb
Width	27.9 cm 11.0 in

Regulatory Compliance/Certifications

Product Specifications



68MCLICK

Agency

ISO 9001:2008

Classification

Designed, manufactured and/or distributed under this quality management system