



912MCLICK

Miniature Click-on Hanger for 9–12 mm cable

Dimensions

Nominal Size	1/4 in 3/8 in
Compatible Diameter, maximum	11.989 mm 0.472 in
Compatible Diameter, minimum	8.992 mm 0.354 in
Height	38.00 mm 1.50 in
Length	43.00 mm 1.69 in
Width	20.00 mm 0.79 in

Electrical Specifications

DTF Effect	0.1 dB
Return Loss Effect	0.1 dB

General Specifications

Hanger Type	Click-on hanger
Cables per Hanger	2
Color	Black
Material Type	Engineered plastic
Maximum Stack Height	3
Ordering Note	CommScope® standard product in Mexico, Central America, and South America
Package Quantity	10

Mechanical Specifications

Mounting	M8 through hole
Operating Temperature	-40 °C to +85 °C (-40 °F to +185 °F)
UV Resistance, minimum with no degradation	=100 hours exposure in accelerated UV life chamber
Vibration Survival	=4 hours at resonant frequency
Environmental Strength Capability	Double cable weight

Packed Dimensions

Height	15.2 cm 6.0 in
Length	2.5 cm 1.0 in
Shipping Weight	0.13 kg 0.29 lb
Width	20.3 cm 8.0 in

Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

Product Specifications



912MCLICK

ISO 9001:2008 Designed, manufactured and/or distributed under this quality management system