



1-1375192-3

**RJ45 Modular Jack, SL Series, Category 3, unshielded, without dust cover, alpine white**

## Body Features

110 Block Material	Polycarbonate
--------------------	---------------

## Configuration Features

Keyed	No
Number of Positions	6
Wiring Pattern	Universal

## Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 $\mu\text{m}$   1.27 $\mu\text{m}$

## Dimensions

Insulated Conductor Outside Diameter	0.057 in   1.45 mm
Solid Wire Range	.51 mm <sup>2</sup>   .65 mm <sup>2</sup>
Stranded Wire Range	.14 mm <sup>2</sup>   .2 mm <sup>2</sup>
Wire Range	22 AWG   24 AWG   26 AWG

## Housing Features

Housing Color	White
Housing Material	Polycarbonate

## Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

## Mechanical Attachment

Mounting Type	SL Series Faceplate
---------------	---------------------

## Other

Comment	With strain relief.
---------	---------------------

## Packaging Features

1-1375192-3

Packaging Method	Poly Bag
Packaging Quantity	1

## Product Availability

Region Asia | Australia/New Zealand | EMEA | Latin America | North America

## Product Type Features

Product Type	Modular Jack
Performance Category	Category 3
Shielded	No
System	AMP NETCONNECT   SL 110 Series
Applies To	Panel
Cable Type	Unshielded Twisted Pair
Connector Style	Jack
Connector Type	Connector Assembly
Dust Cover	Without
Jack Type	RJ11

## Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant