



1-1671226-3

MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Cassette, OM3, MPO to LC-duplex, 12F pair flipped

Body Features

Color	Black
Cable Entry	Front

Configuration Features

Front Connector Type	LC/UPC
Number of Fibers	12
Port Capacity	6
Port Color	Aqua
Port Style	Duplex
Preloaded	Yes

Identification Marking

Labeled	Yes
---------	-----

Mechanical Attachment

Mounting Style	Quick-Fit
----------------	-----------

Operation/Application

AMPTRAC Enabled	No
For Use With	AMP NETCONNECT Quick-Fit Patch Panels with Maximum Density of 4 Cassettes per Unit
SECURE	No
Universal Connectivity Platform	Yes

Other

Comment	Includes 1 MPO Adapter and dust cover
---------	---------------------------------------

Packaging Features

Packaging Method	Individual
Packaging Quantity	1

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Fiber Cassette
System	AMP NETCONNECT MPOptimate® Universal Connectivity Platform (UCP)

1-1671226-3

Adapter Type	MPO to LC
Fiber Diameter	50/125 µm
Fiber Type	OM3
MPO Product	Yes
Optical Mode	Multimode OM3 OM4
Polarity	Pairs Flipped

Signal Characteristics

Ethernet Speed	XG Gb/s
----------------	---------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant