

1-1711027-0

RJ45 Consolidation Point Cable, UTP, white, 10 m

Body Features

Cable Color	White
Shield Style	UTP

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Power Positions	0

Dimensions

Length	10.00 m		32.81 ft
Overall Outside Cable Diameter	5.588 mm		0.220 in
Wire Size (CMA)	.205 mm ²		24 AWG

Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

Operation/Application

Halogen Free	Yes
--------------	-----

Packaging Features

Packaging Method	Bag
------------------	-----

Product Availability

Region	Asia		Australia/New Zealand		EMEA
--------	------	--	-----------------------	--	------

Product Type Features

Product Type	Consolidation Point Cable
System	AMP NETCONNECT
Assembly Type	Plug to Jack
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Jack
Performance Category	Category 6
Cable Assembly Category	Industry Standard
Shielded	No

Usage Conditions

Operating Temperature Range	-20 – 60 °C
-----------------------------	-------------

Regulatory Compliance/Certifications

Agency

Classification

Product Specifications



1-1711027-0

RoHS 2011/65/EU

Compliant