

1-2055725-4

**Multi-Fiber Patch Cord, 12-fiber, OM3, LC/PC-LC/PC, 14 m, aqua**

## Body Features

Cable Color	Aqua
Boot Color (End A)	Aqua
Boot Color (End B)	Aqua
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Connector Color (End A)	Beige
Connector Color (End B)	Beige

## Configuration Features

Number of Fibers	12
Number of Connectors (End A)	12
Number of Connectors (End B)	12

## Dimensions

Assembly Length	14.00 m   45.93 ft
Cable Outer Diameter	.252 in   6.4 mm

## Industry Standards

Flammability Rating	LSZH
---------------------	------

## Product Availability

Region	Australia/New Zealand   EMEA
--------	------------------------------

## Product Type Features

Product Type	Patch Cord (multi-fiber)
System	AMP NETCONNECT   MPOptimate®
Connector Type (End A)	LC/UPC
Connector Type (End B)	LC/UPC
Fiber Type	OM3
Fiber Diameter	50/125 µm
Fiber Cable Buffering	Loose tube, gel-filled
Optical Mode	Multimode
Polarity	Straight

## Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

## \* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---