



1-2153146-0

**Sigma-Link™ Universal Connectivity Platform Q-Fit Cable Assemb., H to H, POF, class EA, 10 m**

## **OBSOLETE**

This product was discontinued on: September 1, 2016

### Replaced By:

1-2153400-0

Sigma-Link™ Universal Connectivity Platform Q-Fit Cable Assembly, STP, class EA, H to H, 10 m

## Body Features

Cable Color White

## Configuration Features

Configuration Double-ended  
Number of Positions Bundle of 6 x 4 pairs

## Dimensions

Length 10.00 m | 32.81 ft

## Industry Standards

Flammability Rating LSFRZH

## Packaging Features

Packaging Method Bag/Carton  
Packaging Quantity 1

## Product Availability

Region Asia | Australia/New Zealand | EMEA | Latin America | North America

## Product Type Features

Product Type Trunk cable  
System AMP NETCONNECT | Sigma-Link™  
Assembly Type Cassette to Cassette  
Connector Type (End A) Sigma-Link Housing  
Connector Type (End B) Sigma-Link Housing  
Performance Category Class EA – link/channel  
Cable Type Twisted Pair  
Shielded Yes

1-2153146-0

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant