



1-2160135-0
MPOptimate® Trunk Cable, 12 fiber, female-female, OM3, straight, 10 m, aqua

Body Features

Cable Color	Aqua
-------------	------

Configuration Features

Number of Fibers	12
Number of Connectors (End A)	1
Number of Connectors (End B)	1

Dimensions

Assembly Length	10.00 m 32.81 ft
-----------------	--------------------

Product Availability

Region	EMEA
--------	------

Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OM3
Fiber Diameter	50/125 µm
Optical Mode	Multimode

Regulatory Compliance/Certifications

Agency RoHS 2011/65/EU	Classification Compliant
----------------------------------	------------------------------------

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---