



1-2160266-5

MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Cassette, MPO/LC, OM4, 24F, pair flipped

Body Features

Color Black

Configuration Features

Front Connector Type LC/UPC
Number of Fibers 24
Port Capacity 12
Port Color Aqua
Port Style Quad
Preloaded Yes

Identification Marking

Labeled Yes

Mechanical Attachment

Mounting Style Quick-Fit

Operation/Application

AMPTRAC Enabled No
For Use With AMP NETCONNECT AMP Hi-D modular MPO panels & the UCP panels
SECURE No
Universal Connectivity Platform Yes

Other

Comment Includes 1 MPO Adapter and dust cover

Packaging Features

Packaging Method Individual
Packaging Quantity 1

Product Availability

Region Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

Product Type Fiber Cassette
System AMP NETCONNECT | MPOptimate® | Universal Connectivity Platform (UCP)
Adapter Type MPO to LC

1-2160266-5

Fiber Diameter	50/125 μ m
Fiber Type	OM4
MPO Product	Yes
Optical Mode	Multimode OM3 OM4
Polarity	Pairs Flipped

Signal Characteristics

Ethernet Speed	10 Gb/s
----------------	---------

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant