

1-336488-1

RJ45 Patch Cord, category 6A, S/FTP, stranded, white, 0.5 m

Body Features

Cable Color	White
Shield Style	S/FTP
Conductor Material	Copper

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Power Positions	0

Dimensions

Length	0.50 m 1.64 ft
Overall Outside Cable Diameter	5.900 mm 0.232 in
Wire Size (CMA)	.129 – .205 mm ² 26 – 24 AWG

Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

Operation/Application

Halogen Free	Yes
--------------	-----

Packaging Features

Packaging Method	Bag
------------------	-----

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Consolidation Point Cable
System	AMP NETCONNECT AMP-TWIST
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	4P AMP-TWIST Plug
Performance Category	Category 6A
Cable Assembly Category	Industry Standard
Shielded	Yes

Usage Conditions

Operating Temperature Range	-20 – 60 °C
-----------------------------	-------------

Regulatory Compliance/Certifications

Product Specifications



1-336488-1

Agency

RoHS 2011/65/EU

Classification

Compliant