

1-599623-7

**Fiber Optic Cable, 6-fiber, OM2, 1000 m, orange**

## Body Features

Cable Color	Orange
Cable Construction	1 x 6
Bend Radius (Installation)	130.05 mm   5.12 in
Bend Radius (Long Term)	80.00 mm   3.15 in
Tensile Strength (Installation)	1249.95 N   281.00 lbf
Tensile Strength (Long Term)	650.00 N   146.13 lbf
Weight (Nominal)	48.0 kg/km

## Configuration Features

Number of Fibers	6
Number of Fillers	1

## Dimensions

Length	1000.00 m   3280.83 ft
Outside Diameter	6.40 mm   0.25 in

## Industry Standards

Flammability Rating	ULSZH (Universal Low Smoke Zero Halogen)
---------------------	--

## Operation/Application

Environment	Outdoor
-------------	---------

## Product Availability

Region	Asia   Australia/New Zealand   EMEA
--------	-------------------------------------

## Product Type Features

Product Type	Cable
Fiber Type	OM2
Armoring	None
Cable Type	Fiber Optic
Fiber Cable Buffering	Loose tube, gel-filled
Fiber Diameter	50/125 $\mu$ m
Fiber Specification	IEC 60794-1
System	AMP NETCONNECT

## Signal Characteristics

Attenuation, maximum (1300nm)	1.00 dB/km
Attenuation, maximum (850nm)	3.50 dB/km

## Usage Conditions

1-599623-7

Installation Temperature Range -5 – 50 °C  
Operating Temperature Range -20 – 70 °C | -4 – 158 °F  
Storage Temperature Range -20 – 70 °C

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant