



1-6536501-0

Fiber Optic Patch Cord, singlemode, 1.8 mm zipcord, LC/PC to LC/PC duplex tuned, 10 m, yellow

Body Features

Cable Color	Yellow
Boot Color (End A)	Blue
Boot Color (End B)	Blue
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Connector Color (End A)	Blue
Connector Color (End B)	Blue

Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	10.00 m 32.81 ft
Cable Outer Diameter	.071 in 1.8 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT
Connector Type (End A)	LC/UPC
Connector Type (End B)	LC/UPC
Fiber Type	OS2
Fiber Diameter	9/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer

1-6536501-0

Fiber Cable Type	Duplex, dualzip
Optical Mode	Singlemode
Polarity	Pair Flipped

Signal Characteristics

Return Loss, minimum	45 dB
----------------------	-------

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---