

1-6536967-0

Fiber Optic Patch Cord, LC to SC, twin zip, 10 m, aqua

Body Features

Cable Color	Aqua
Boot Color (End A)	Beige
Boot Color (End B)	Black
Boot Type (End A)	Bend limiting
Boot Type (End B)	Bend limiting
Connector Color (End A)	Beige
Connector Color (End B)	Beige

Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	10.00 m 32.81 ft
Cable Outer Diameter	.071 x .142 in 1.8 x 3.6 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Asia Australia/New Zealand EMEA
--------	-------------------------------------

Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT
Connector Type (End A)	LC/UPC
Connector Type (End B)	SC/UPC
Fiber Type	OM3
Fiber Diameter	50/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Duplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Multimode
Polarity	Pair Flipped

Signal Characteristics

Insertion Loss, maximum (End A)	0.30 dB
---------------------------------	---------

1-6536967-0

Insertion Loss, maximum (End B) 0.30 dB

Return Loss, minimum 30 dB

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

* Footnotes

Assembly Length Assembly length includes the breakout lengths