

1-6695657-0

Fiber Optic Patch Cord, singlemode, 1.8 mm tuned zipcord, LC/PC duplex-2xST/PC simplex, 10 m, yellow

OBSOLETE

This product was discontinued on: October 1, 2016

Body Features

Cable Color	Yellow
Boot Color (End A)	Blue
Boot Color (End B)	Red/Black
Boot Type (End A)	Bend limiting
Boot Type (End B)	Push-on
Connector Color (End A)	Blue

Configuration Features

Number of Fibers	2
Number of Connectors (End A)	2
Number of Connectors (End B)	2

Dimensions

Assembly Length	10.00 m 32.81 ft
Cable Outer Diameter	1.8 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Patch Cord (duplex)
System	AMP NETCONNECT MPOptimate®
Connector Type (End A)	LC/UPC
Connector Type (End B)	ST/UPC
Fiber Type	OS2
Fiber Diameter	9/125 µm
Connector Style (End A)	Duplex
Connector Style (End B)	Simplex
Ferrule Material	Ceramic
Fiber Cable Buffering	Tight buffer
Fiber Cable Type	Duplex, dualzip
Optical Mode	Singlemode

1-6695657-0

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---