

**1206505-8****Fiber Optic Termination Panel, 1U, 19 in, 12 SC/UPC adapters, black**

Body Features

| | |
|---------------|---------------|
| Cable Entry | Rear |
| Cable Exit | Rear |
| Chassis Color | Black |
| Finish | Powder coated |

Configuration Features

| | |
|----------------------|---------------|
| Front Connector Type | SC/UPC |
| Splice Chip Type | Mechanical |
| Configuration | Adapters only |
| Port Style | Duplex |
| Splice Capacity | 4 |

Dimensions

| | |
|--------|------------------------|
| Height | 44.450 mm 1.750 in |
| Width | 482.600 mm 19.000 in |

Other

| | |
|---------|---|
| Comment | With 12 Preinstalled Blanking Plugs (Dust Covers) |
|---------|---|

Packaging Features

| | |
|--------------------|--|
| Includes | Installation Instruction Mounting hardware |
| Packaging Method | Box/Carton |
| Packaging Quantity | 1 |

Product Availability

| | |
|--------|------|
| Region | EMEA |
|--------|------|

Product Type Features

| | |
|--------------|-------------------------|
| Product Type | Fiber Termination Panel |
| System | AMP NETCONNECT |
| Rack Units | 1.0 |
| Optical Mode | Multimode |

Regulatory Compliance/Certifications

| |
|----------------------------------|
| Agency RoHS 2011/65/EU |
|----------------------------------|

| |
|------------------------------------|
| Classification Compliant |
|------------------------------------|