



1375165-1
Vertical Finger Duct Panel, 35 in, side mount

Body Features

| | |
|----------|----------|
| Color | Black |
| Material | Aluminum |

Configuration Features

| | |
|-----------------------|------------------|
| Cable Management Type | Vertical |
| Cable Routing (Front) | Standard fingers |
| Cable Routing (Rear) | Standard fingers |
| Configuration | Single-sided |

Dimensions

| | |
|--------------|-----------------------|
| Height | 159.512 mm 6.280 in |
| Panel Height | 88.900 mm 3.500 in |

Housing Features

| | |
|---------------|------|
| Housing Color | Aqua |
|---------------|------|

Mechanical Attachment

| | |
|-----------------|-----------|
| Mount Alignment | Half Rack |
|-----------------|-----------|

Operation/Application

| | |
|--------------|-------------------------------------|
| For Use With | Twisted Pair & Optical Fiber Cables |
|--------------|-------------------------------------|

Other

| | |
|-------------|----|
| UCP Product | No |
|-------------|----|

Product Availability

| | |
|--------|---|
| Region | Asia Australia/New Zealand EMEA Latin America North America |
|--------|---|

Product Type Features

| | |
|--------------|------------------------|
| Product Type | Cable Management Panel |
| System | AMP NETCONNECT |

Regulatory Compliance/Certifications

| | |
|----------------------------------|------------------------------------|
| Agency RoHS 2011/65/EU | Classification Compliant |
|----------------------------------|------------------------------------|