

1375187-7

**SL110 Series Modular Jack, 8-position, RJ45, category 6, T568A/T568B, unshielded, with dust cover, red**

## Body Features

110 Block Material	Polycarbonate
Cover Color	Transparent
Cover Material	Polycarbonate

## Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

## Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin   1.27 µm

## Dimensions

Insulated Conductor Outside Diameter	0.057 in   1.45 mm
Solid Wire Range	24 – 22 AWG
Stranded Wire Range	26 – 24 AWG

## Housing Features

Housing Color	Red
Housing Material	Polycarbonate

## Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

## Other

Comment	With strain relief.
---------	---------------------

## Packaging Features

Packaging Method	Poly Bag
Packaging Quantity	1

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## Product Type Features

Product Type	Modular Jack
Performance Category	Category 6

1375187-7

Shielded	No
System	AMP NETCONNECT   SL 110 Series
Applies To	Panel
Connector Style	Jack
Connector Type	Connector Assembly
Dust Cover	With
Jack Type	RJ45

## Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

## Regulatory Compliance/Certifications

<b>Agency</b>	<b>Classification</b>
RoHS 2011/65/EU	Compliant