

1375190-6

SL110 Series Modular Jack, RJ45, category 5e, T568A/T568B, unshielded, with dust cover, blue

OBSOLETE

This product was discontinued on: February 28, 2017

Replaced By:

1375187-6

SL110 Series Modular Jack, RJ45, category 6, T568A/T568B, unshielded, with dust cover, blue

Body Features

110 Block Material	Polycarbonate
Cover Color	Transparent
Cover Material	Polycarbonate

Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin 1.27 µm

Dimensions

Insulated Conductor Outside Diameter	0.057 in 1.45 mm
Solid Wire Range	24 – 22 AWG
Stranded Wire Range	26 – 24 AWG

Housing Features

Housing Color	Blue
Housing Material	Polycarbonate

Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

Other

Comment	With strain relief.
---------	---------------------

Packaging Features

Packaging Method	Poly Bag
Packaging Quantity	1

13751906

Product Availability

Region Asia | Australia/New Zealand | EMEA | Latin America | North America

Product Type Features

Product Type	Modular Jack
Performance Category	Category 5e
Shielded	No
System	AMP NETCONNECT SL 110 Series
Applies To	Panel
Connector Style	Jack
Connector Type	Connector Assembly
Dust Cover	With
Jack Type	RJ45

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant