

1499631-2

**KL110 Series Modular Jack, 8-position, RJ45, category 6, black**

## Body Features

110 Block Material	Polycarbonate
Cover Material	Polycarbonate

## Configuration Features

Keyed	No
Number of Positions	8
Wiring Pattern	Universal

## Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin   1.27 µm

## Dimensions

Insulated Conductor Outside Diameter	0.057 in   1.45 mm
Solid Wire Range	.51 mm <sup>2</sup>   .65 mm <sup>2</sup>
Stranded Wire Range	.14 mm <sup>2</sup>   .2 mm <sup>2</sup>
Wire Range	22 AWG   24 AWG   26 AWG

## Housing Features

Housing Color	Black
Housing Material	Polycarbonate

## Industry Standards

UL Flammability Rating	UL 94V-0
------------------------	----------

## Other

Comment	With strain relief.
---------	---------------------

## Packaging Features

Packaging Method	Poly Bag
Packaging Quantity	1

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   Latin America   North America
--------	---

## Product Type Features

Product Type	Modular Jack
Performance Category	Category 6

1499631-2

Shielded	No
System	AMP NETCONNECT   KL 110 Series
Applies To	Panel
Cable Type	Unshielded Twisted Pair
Connector Style	Jack
Connector Type	Connector Assembly
Dust Cover	Without
Jack Type	RJ45

## Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	110 Style Punch-Down   SL Termination Tool

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant