

**1553533-2****Fiber Optic Termination Panel, 1U MPO to Quad LC, 19 in OM3/OM4 multimode, 48-port****OBSOLETE**

Body Features

Chassis Color	Black
Finish	Powder coated

Configuration Features

Front Connector Type	LC/UPC
Configuration	Adapters only
Number of Fibers	64
Rear/Far End Connector Type	MPO

Dimensions

Height	44.450 mm 1.750 in
Width	482.600 mm 19.000 in

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	Asia Australia/New Zealand EMEA Latin America North America
--------	---

Product Type Features

Product Type	Fiber Termination Panel
System	AMP NETCONNECT
Rack Units	1.0
Fiber Type	OM3
Optical Mode	Multimode

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant