



1671196-3

Universal Connectivity Platform (UCP) Q-Fit Module, 12F, MM OM3, 6 duplex ports

Body Features

Color	Black
Sleeve Material	Ceramic

Configuration Features

Front Connector Type	LC/UPC
Number of Fibers	12
Port Capacity	6
Port Color	Aqua
Port Style	Duplex
Preloaded	Yes

Mechanical Attachment

Mounting Style	Snap-In
Mounts To	Rack

Operation/Application

Accepts	LC Patch Cords
AMPTRAC Enabled	No
SECURE	No
Universal Connectivity Platform	Yes

Packaging Features

Packaging Method	Box
Packaging Quantity	1

Product Availability

Region	Asia
--------	------

Product Type Features

Product Type	Adapter Plate
System	AMP NETCONNECT MPOptimate® Universal Connectivity Platform (UCP)
Adapter Type	LC
Enclosure Type	Patch
Fiber Type	OM3
Optical Mode	Multimode OM3 OM4

Signal Characteristics

1671196-3

Ethernet Speed	XG Gb/s
----------------	---------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant