



1671207-3

MPOptimate® Universal Connectivity Platform (UCP) Q-Fit Cassette, MPO to 6xSC-duplex, OM3, pair straight

Body Features

Color	Black
Cable Entry	Front

Configuration Features

Front Connector Type	SC/UPC
Number of Fibers	12
Port Capacity	6
Port Color	Aqua
Port Style	Duplex
Preloaded	Yes

Mechanical Attachment

Mounting Style	Quick-Fit
----------------	-----------

Operation/Application

Accepts	MPO Adapter Plate
AMPTRAC Enabled	No
For Use With	AMP NETCONNECT Quick-Fit Patch Panels with Maximum Density of 4 Cassettes per Unit
SECURE	No
Universal Connectivity Platform	Yes

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Availability

Region	Australia/New Zealand EMEA Latin America North America
--------	--

Product Type Features

Product Type	Fiber Cassette
System	AMP NETCONNECT MPOptimate® Universal Connectivity Platform (UCP)
Adapter Type	MPO to LC MPO to SC
Fiber Diameter	50/125 µm
Fiber Type	OM3
MPO Product	Yes
Optical Mode	Multimode OM3 OM4
Polarity	Pairs Straight

1671207-3

Signal Characteristics

Ethernet Speed	10 Gb/s
----------------	---------

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant