

1711027-5

**RJ45 Consolidation Point, UTP, solid, white, 5 m**

## Body Features

Cable Color	White
Shield Style	UTP

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Number of Power Positions	0

## Dimensions

Length	5.00 m   16.40 ft
Overall Outside Cable Diameter	5.588 mm   0.220 in
Wire Size (CMA)	.205 mm <sup>2</sup>   24 AWG

## Industry Standards

Flammability Rating	LSZH (Low Smoke Zero Halogen)
---------------------	-------------------------------

## Operation/Application

Halogen Free	Yes
--------------	-----

## Packaging Features

Packaging Method	Bag
------------------	-----

## Product Availability

Region	Asia   Australia/New Zealand   EMEA
--------	-------------------------------------

## Product Type Features

Product Type	Consolidation Point Cable
System	AMP NETCONNECT
Assembly Type	Plug to Jack
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Jack
Performance Category	Category 6
Cable Assembly Category	Industry Standard
Shielded	No

## Usage Conditions

Operating Temperature Range	-20 – 60 °C
-----------------------------	-------------

## Regulatory Compliance/Certifications

# Product Specifications



1711027-5

---

**Agency**

RoHS 2011/65/EU

---

**Classification**

Compliant