



1711716-1

AMP-TWIST SL-Series Modular Jack, category 6AS, shielded, 8-position, without dust cover

Body Features

110 Block Material	Polycarbonate
--------------------	---------------

Configuration Features

Keyed	No
Number of Positions	8
Port Configuration	Single
Wiring Pattern	Universal

Contact Features

Contact Base Material	Beryllium copper
Contact Mating Area Plating Material	Gold
Contact Mating Area Plating Thickness	50.00 µin 1.27 µm

Dimensions

Cable Diameter (Max)	9.0 mm 0.4 in
Height	21.500 mm 0.846 in
Insulated Conductor Outside Diameter	0.0629 in 1.6 mm
PCB Thickness (Recommended)	1.600 mm 0.063 in
Solid Wire Range	24 – 22 AWG
Stranded Wire Range	26 – 24 AWG

Housing Features

Housing Color	Gray
Housing Material	Zamak 5

Other

Comment	Rear Exit
---------	-----------

Packaging Features

Packaging Method	Box Tray/Box
Packaging Quantity	12

1711716-1

Product Availability

Region Asia | Australia/New Zealand | EMEA

Product Type Features

Product Type	Modular Jack
Performance Category	Category 6A
Shielded	Yes
System	AMP NETCONNECT AMP-TWIST Series SL Series
Applies To	Panel
Connector Style	Jack
Connector Type	Connector Assembly
Dust Cover	Without
Jack Type	RJ45

Termination Features

Termination Method to Wire/Cable	Insulation Displacement Crimp (IDC)
Termination Style	SL Termination Tool

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant