

**1828953-3****LightCrimp Plus™ Fiber Optic ST Connector Kit, OS2, blue**

## Body Features

Body Material	Aluminum
Body Plating Material	Nickel
Boot Color	Black
Boot Material	Thermoplastic elastomer (TPE)
Boot Type	Bend limiting
Epoxyless	Yes
Ferrule Hole Size	125.0 µm
Sleeve Material	Copper

## Dimensions

Outside Cable Diameter (Max) 3.0 mm | 0.1 in

## Identification Marking

AMP Logo	Yes
----------	-----

## Mechanical Attachment

Coupling Nut Material	Zinc
-----------------------	------

## Packaging Features

Packaging Method	Package
Packaging Quantity	1

## Product Availability

Region	Asia   Australia/New Zealand   EMEA   North America
--------	---

## Product Type Features

Product Type	Connector
Connector Type	ST
Optical Mode	Singlemode
Connector Style	Simplex
Fiber Type	OS2
System	AMP NETCONNECT   LIGHTCRIMP PLUS
Booted	Yes
Ferrule Material	Ceramic
Pre-Polished	Yes

## Signal Characteristics

1828953-3

---

Insertion Loss (Max)	0.75 dB
----------------------	---------

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant