



1859007-7

**RJ45 Patch Cord, category 6, 8-port, SL boot, gray, 7 ft**

## Body Features

Cable Color                      Gray

## Configuration Features

Configuration                      Double-ended  
Keyed                                  No  
Number of Positions                4-pair  
Number of Power Positions        0  
Wiring Pattern                      T568B

## Dimensions

Length                                7.00 m | 22.97 ft  
Overall Outside Cable Diameter    5.588 mm | 0.220 in  
Wire Size (CMA)                    .205 mm<sup>2</sup> | 24 AWG

## Industry Standards

Flammability Rating                Non-Plenum (CM Rated)

## Packaging Features

Packaging Method                  Bag

## Product Availability

Region                                Asia

## Product Type Features

Product Type                        Patch Cord  
System                                AMP NETCONNECT  
Assembly Type                        Plug to Plug  
Connector Type (End A)              RJ45 Modular Plug  
Connector Type (End B)              RJ45 Modular Plug  
Performance Category                Category 6  
Cable Assembly Category            Industry Standard  
Shielded                                No

## Regulatory Compliance/Certifications

Agency	Classification
--------	----------------

# Product Specifications



1859007-7

RoHS 2011/65/EU

Compliant