

**1859238-8****RJ45 Patch Cord, category 5e, 8-port, trans SL boot, gray, 8 ft**

Body Features

| | |
|--------------------|----------|
| Cable Color | Gray |
| Conductor Material | Copper |
| Conductor Type | Stranded |

Configuration Features

| | |
|---------------------|--------------|
| Configuration | Double-ended |
| Keyed | No |
| Number of Positions | 4-pair |
| Wiring Pattern | T568A |

Dimensions

| | |
|--------------------------------|---------------------|
| Length | 2.44 m 8.00 ft |
| Overall Outside Cable Diameter | 5.400 mm 0.213 in |
| Wire Size (CMA) | 24 AWG |

Industry Standards

| | |
|---------------------|-----------------------|
| Flammability Rating | Non-Plenum (CM Rated) |
|---------------------|-----------------------|

Operation/Application

| | |
|----------------------------|------------|
| Halogen Free | No |
| Plug Insertion Cycles (>=) | 750 cycles |

Packaging Features

| | |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|

Product Availability

| | |
|--------|------|
| Region | Asia |
|--------|------|

Product Type Features

| | |
|------------------------|-------------------|
| Product Type | Patch Cord |
| System | AMP NETCONNECT |
| Assembly Type | Plug to Plug |
| Connector Type (End A) | RJ45 Modular Plug |
| Connector Type (End B) | RJ45 Modular Plug |
| Performance Category | Category 5e |

1859238-8

| | |
|-------------------------|-------------------|
| Cable Assembly Category | Industry Standard |
| Shielded | No |

Usage Conditions

Operating Temperature Range -20 – 60 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant