



1859239-6

RJ45 Patch Cord, category 5e, 8-port, trans SL boot, blue, 6 ft

Body Features

Cable Color	Blue
Conductor Material	Copper
Conductor Type	Stranded

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Wiring Pattern	T568A

Dimensions

Length	1.83 m 6.00 ft
Overall Outside Cable Diameter	5.400 mm 0.213 in
Wire Size (CMA)	24 AWG

Industry Standards

Flammability Rating	Non-Plenum (CM Rated)
---------------------	-----------------------

Operation/Application

Halogen Free	No
Plug Insertion Cycles (>=)	750 cycles

Packaging Features

Packaging Method	Bag
------------------	-----

Product Availability

Region	Asia
--------	------

Product Type Features

Product Type	Patch Cord
System	AMP NETCONNECT
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug

1859239-6

Performance Category	Category 5e
Cable Assembly Category	Industry Standard
Shielded	No

Usage Conditions

Operating Temperature Range -20 – 60 °C

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant