



1859239-8

**RJ45 Patch Cord, category 5e, 8-port, trans SL boot, blue, 8 ft**

## Body Features

Cable Color	Blue
Conductor Material	Copper
Conductor Type	Stranded

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Wiring Pattern	T568A

## Dimensions

Length	2.44 m   8.00 ft
Overall Outside Cable Diameter	5.400 mm   0.213 in
Wire Size (CMA)	24 AWG

## Industry Standards

Flammability Rating	Non-Plenum (CM Rated)
---------------------	-----------------------

## Operation/Application

Halogen Free	No
Plug Insertion Cycles (>=)	750 cycles

## Packaging Features

Packaging Method	Bag
------------------	-----

## Product Availability

Region	Asia
--------	------

## Product Type Features

Product Type	Patch Cord
System	AMP NETCONNECT
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug

1859239-8

Performance Category	Category 5e
Cable Assembly Category	Industry Standard
Shielded	No

## Usage Conditions

---

Operating Temperature Range -20 – 60 °C

## Regulatory Compliance/Certifications

---

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant