



1859241-3

RJ45 Patch Cord, category 5e, 8-port, trans SL boot, red, 3 ft

Body Features

Cable Color Red

Configuration Features

Configuration Double-ended
Keyed No
Number of Positions 4-pair
Number of Power Positions 0
Wiring Pattern T568A

Dimensions

Length 3.00 m | 9.84 ft
Wire Size (CMA) .205 mm² | 24 AWG

Industry Standards

Flammability Rating Non-Plenum (CM Rated)

Packaging Features

Packaging Method Bag

Product Availability

Region Asia

Product Type Features

Product Type Patch Cord
System AMP NETCONNECT
Assembly Type Plug to Plug
Connector Type (End A) RJ45 Modular Plug
Connector Type (End B) RJ45 Modular Plug
Performance Category Category 5e
Cable Assembly Category Industry Standard
Shielded No

Usage Conditions

Operating Temperature Range -40 – 70 °C

1859241-3

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant