



1859241-4

RJ45 Patch Cord, category 5e, 8-port, trans SL boot, red, 4 ft

Body Features

Cable Color	Red
-------------	-----

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Number of Power Positions	0
Wiring Pattern	T568A

Dimensions

Length	4.00 m 13.12 ft
Wire Size (CMA)	.205 mm ² 24 AWG

Industry Standards

Flammability Rating	Non-Plenum (CM Rated)
---------------------	-----------------------

Operation/Application

Halogen Free	No
--------------	----

Packaging Features

Packaging Method	Bag
------------------	-----

Product Availability

Region	Asia
--------	------

Product Type Features

Product Type	Patch Cord
System	AMP NETCONNECT
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 5e
Cable Assembly Category	Industry Standard
Shielded	No

1859241-4

Usage Conditions

Operating Temperature Range -40 – 70 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant