

**1859243-6****RJ45 Patch Cord, category 5e, 8-port, trans SL boot, yellow, 6 ft**

Body Features

Cable Color	Yellow
Conductor Material	Copper
Conductor Type	Stranded

Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Wiring Pattern	T568A

Dimensions

Length	1.83 m 6.00 ft
Overall Outside Cable Diameter	5.400 mm 0.213 in
Wire Size (CMA)	24 AWG

Industry Standards

Flammability Rating	Non-Plenum (CM Rated)
---------------------	-----------------------

Operation/Application

Halogen Free	No
Plug Insertion Cycles (>=)	750 cycles

Packaging Features

Packaging Method	Bag
------------------	-----

Product Availability

Region	Asia
--------	------

Product Type Features

Product Type	Patch Cord
System	AMP NETCONNECT
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 5e
Cable Assembly Category	Industry Standard

1859243-6

Shielded

No

Usage Conditions

Operating Temperature Range -20 – 60 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant