

**1859246-3****RJ45 Patch Cord, category 6, 8-port, trans SL boot, gray, 3 ft**

## Body Features

Cable Color	Gray
Conductor Material	Copper
Conductor Type	Stranded

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Wiring Pattern	T568B

## Dimensions

Length	0.91 m   3.00 ft
Overall Outside Cable Diameter	5.600 mm   0.220 in
Wire Size (CMA)	24 AWG

## Industry Standards

Flammability Rating	Non-Plenum (CM Rated)
---------------------	-----------------------

## Operation/Application

Plug Insertion Cycles (>=)	750 cycles
----------------------------	------------

## Packaging Features

Packaging Method	Bag
------------------	-----

## Product Availability

Region	Asia
--------	------

## Product Type Features

Product Type	Patch Cord
System	AMP NETCONNECT
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 6
Cable Assembly Category	Industry Standard

# Product Specifications



---

1859246-3

Shielded

No

## Usage Conditions

---

Operating Temperature Range -20 – 60 °C

## Regulatory Compliance/Certifications

---

### Agency

RoHS 2011/65/EU

### Classification

Compliant