

**1859246-7****RJ45 Patch Cord, category 6, 8-port, trans SL boot, gray, 7 ft**

Body Features

| | |
|-------------|------|
| Cable Color | Gray |
|-------------|------|

Configuration Features

| | |
|---------------------------|--------------|
| Configuration | Double-ended |
| Keyed | No |
| Number of Positions | 4-pair |
| Number of Power Positions | 0 |
| Wiring Pattern | T568B |

Dimensions

| | |
|-----------------|-------------------------------|
| Length | 2.13 m 7.00 ft |
| Wire Size (CMA) | .205 mm ² 24 AWG |

Industry Standards

| | |
|---------------------|-----------------------|
| Flammability Rating | Non-Plenum (CM Rated) |
|---------------------|-----------------------|

Operation/Application

| | |
|--------------|----|
| Halogen Free | No |
|--------------|----|

Packaging Features

| | |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|

Product Availability

| | |
|--------|------|
| Region | Asia |
|--------|------|

Product Type Features

| | |
|-------------------------|-------------------|
| Product Type | Patch Cord |
| System | AMP NETCONNECT |
| Assembly Type | Plug to Plug |
| Connector Type (End A) | RJ45 Modular Plug |
| Connector Type (End B) | RJ45 Modular Plug |
| Performance Category | Category 6 |
| Cable Assembly Category | Industry Standard |
| Shielded | No |

1859246-7

Usage Conditions

Operating Temperature Range -40 – 70 °C

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant