

**1918385-1****Fiber Optic Connector Kit, LC, MM, 900 µm, simplex**

Body Features

Boot Color	Beige
Boot Type	Short
Connector Color	Beige
Epoxyless	No

Dimensions

Boot Length	10.25 mm 0.40 in
Cable Outer Diameter	.035 in .90 mm

Mechanical Attachment

Flanged	No
---------	----

Operation/Application

SECURE	No
--------	----

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Availability

Region	Asia Australia/New Zealand EMEA North America
--------	---

Product Type Features

Product Type	Connector
Connector Type	LC UPC
Optical Mode	Multimode
Cable Type	Buffered Fiber
Connector Style	Simplex
Fiber Type	OM1
System	AMP NETCONNECT
Fiber Diameter	62.5 µm
Pre-Polished	No

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant