Product Specifications



1918385-3

Fiber Optic OM3 and OM4 Multimode Epoxy/Polish Connector, LC simplex, aqua

Body Features

Boot Color	Aqua
Boot Type	Short
Connector Color	Aqua
Epoxyless	No

Dimensions

Boot Length	10.25 mm | 0.40 in
Cable Outer Diameter	.035 in | .90 mm

Mechanical Attachment

Flanged	No

Operation/Application

SECURE	No

Packaging Features

Packaging Method	Bag
Packaging Quantity	1

Product Availability

Region	Asia | Australia/New Zealand | EMEA | North America

Product Type Features

Product Type	Connector
Connector Type	LC UPC
Optical Mode	Multimode
Cable Type	Buffered Fiber
Connector Style	Simplex
Fiber Type	OM3/OM4
System	AMP NETCONNECT
Fiber Diameter	50 µm
Pre-Polished	No

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

©2017 CommScope, Inc. All rights reserved. All trademarks identified by ® or ™ are registered trademarks, respectively, of CommScope.
All specifications are subject to change without notice. See www.commscope.com for the most current information. Revised: May 19, 2017