

**1918627-2****LightCrimp Plus™ Fiber Optic Kit, LC, simplex, 50/125 µm, jacketed**

Body Features

Boot Color	Black
Connector Color	Beige
Epoxyless	Yes

Dimensions

Boot Length	25.40 mm 1.00 in
Cable Outer Diameter	.062 in 1.6 – 2 mm

Mechanical Attachment

Flanged	No
---------	----

Operation/Application

SECURE	No
--------	----

Packaging Features

Packaging Method	Package
Packaging Quantity	1

Product Availability

Region	Asia Australia/New Zealand EMEA North America
--------	---

Product Type Features

Product Type	Connector
Connector Type	LC UPC
Optical Mode	Multimode
Cable Type	Jacketed Cable
Connector Style	Simplex
Fiber Type	OM2
System	AMP NETCONNECT
Fiber Diameter	50 µm
Pre-Polished	Yes

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant