

**1918781-1****Fiber Optic MPO-LC Cassette, 6-port, 62.5**

Body Features

Color	Black
-------	-------

Configuration Features

Front Connector Type	LC/UPC
Number of Fibers	12
Port Capacity	6
Port Color	Beige
Port Style	Duplex
Preloaded	Yes

Identification Marking

Labeled	Yes
---------	-----

Mechanical Attachment

Mounting Style	Snap-In
----------------	---------

Operation/Application

SECURE	No
Universal Connectivity Platform	No

Packaging Features

Packaging Method	Carton
Packaging Quantity	1

Product Availability

Region	Asia Latin America North America
--------	--------------------------------------

Product Type Features

Product Type	Fiber Cassette
System	AMP NETCONNECT
Adapter Type	MPO to LC
Fiber Diameter	62.5/125 μ m
Fiber Type	OM1
Optical Mode	Multimode
Polarity	Pairs Flipped

1918781-1

Regulatory Compliance/Certifications

Agency

RoHS 2011/65/EU

Classification

Compliant