



1918785-2

**MPOptimate® Singlemode Cassettes, 12 fiber, 12 LC/UPC SM adapters 1, SM fiber, angle right, red**

## Body Features

Color	Red
Cable Entry	Rear
Cable Exit	Rear

## Configuration Features

Front Connector Type	LC/UPC
Number of Cable Feeds	2
Number of Fibers	24
Port Capacity	12
Port Color	Red
Port Style	Duplex
Preloaded	Yes

## Identification Marking

Labeled	Yes
---------	-----

## Mechanical Attachment

Mounting Style	Snap-In
----------------	---------

## Operation/Application

SECURE	Yes
Universal Connectivity Platform	No

## Other

Comment	MPO coupling bushing is standard black
---------	--

## Packaging Features

Packaging Method	Carton
Packaging Quantity	1

## Product Availability

Region	Australia/New Zealand   EMEA   Latin America   North America
--------	--

## Product Type Features

Product Type	Fiber Cassette
System	AMP NETCONNECT

1918785-2

Adapter Type	MPO to LC
Fiber Diameter	50/125 $\mu$ m
Fiber Type	OM3
MPO Product	Yes
Optical Mode	Multimode
Polarity	Pairs Flipped

## Signal Characteristics

Ethernet Speed	XG Gb/s
----------------	---------

## Regulatory Compliance/Certifications

### Agency

RoHS 2011/65/EU

### Classification

Compliant