



1918785-3

MPOptimate® Singlemode Cassettes, 12 fiber, 12 LC/UPC SM adapters 1, SM fiber, angle right, green

Body Features

| | |
|-------------|-------|
| Color | Green |
| Cable Entry | Rear |
| Cable Exit | Rear |

Configuration Features

| | |
|-----------------------|--------|
| Front Connector Type | LC/UPC |
| Number of Cable Feeds | 2 |
| Number of Fibers | 24 |
| Port Capacity | 12 |
| Port Color | Green |
| Port Style | Duplex |
| Preloaded | Yes |

Identification Marking

| | |
|---------|-----|
| Labeled | Yes |
|---------|-----|

Mechanical Attachment

| | |
|----------------|---------|
| Mounting Style | Snap-In |
|----------------|---------|

Operation/Application

| | |
|---------------------------------|-----|
| SECURE | Yes |
| Universal Connectivity Platform | No |

Other

| | |
|---------|--|
| Comment | MPO coupling bushing is standard black |
|---------|--|

Packaging Features

| | |
|--------------------|--------|
| Packaging Method | Carton |
| Packaging Quantity | 1 |

Product Availability

| | |
|--------|--|
| Region | Australia/New Zealand EMEA Latin America North America |
|--------|--|

Product Type Features

| | |
|--------------|----------------|
| Product Type | Fiber Cassette |
| System | AMP NETCONNECT |

1918785-3

| | |
|----------------|----------------------|
| Adapter Type | MPO to LC |
| Fiber Diameter | 50/125 μm |
| Fiber Type | OM3 |
| MPO Product | Yes |
| Optical Mode | Multimode |
| Polarity | Pairs Flipped |

Signal Characteristics

| | |
|----------------|---------|
| Ethernet Speed | XG Gb/s |
|----------------|---------|

Regulatory Compliance/Certifications

| Agency | Classification |
|-----------------|----------------|
| RoHS 2011/65/EU | Compliant |