



1933882-5

**RJ45 Patch Cord, category 6A, shielded, blue, 5 m**

## Body Features

Cable Color	Blue
Shield Style	F/UTP
Conductor Material	Tinned copper
Conductor Type	Stranded

## Configuration Features

Configuration	Double-ended
Keyed	No
Number of Positions	4-pair
Number of Power Positions	0
Wiring Pattern	T568B

## Dimensions

Length	5.00 m   16.40 ft
Overall Outside Cable Diameter	6.000 mm   0.236 in
Wire Size (CMA)	.129 mm <sup>2</sup>   26 AWG

## Industry Standards

Flammability Rating	Non-Plenum (CM Rated)
---------------------	-----------------------

## Operation/Application

Halogen Free	No
--------------	----

## Other

Comment	North America has a corresponding part available under the TCPC-6ARFVB numbering scheme.
---------	--

## Packaging Features

Packaging Method	Bag
------------------	-----

## Product Availability

Region	Asia
--------	------

## Product Type Features

1933882-5

Product Type	Patch Cord
System	AMP NETCONNECT
Assembly Type	Plug to Plug
Connector Type (End A)	RJ45 Modular Plug
Connector Type (End B)	RJ45 Modular Plug
Performance Category	Category 6A
Cable Assembly Category	Industry Standard
Shielded	Yes

## Usage Conditions

Operating Temperature Range	-20 – 60 °C   -4 – 140 °F
Storage Temperature	-20 – 80 °C   -4 – 176 °F

## Regulatory Compliance/Certifications

**Agency**  
RoHS 2011/65/EU

**Classification**  
Compliant