

**1933883-5****RJ45 Patch Cord, category 6A, shielded, green, 5 m**

Body Features

| | |
|--------------------|---------------|
| Cable Color | Green |
| Shield Style | F/UTP |
| Conductor Material | Tinned copper |
| Conductor Type | Stranded |

Configuration Features

| | |
|---------------------------|--------------|
| Configuration | Double-ended |
| Keyed | No |
| Number of Positions | 4-pair |
| Number of Power Positions | 0 |
| Wiring Pattern | T568B |

Dimensions

| | |
|--------------------------------|-------------------------------|
| Length | 5.00 m 16.40 ft |
| Overall Outside Cable Diameter | 6.000 mm 0.236 in |
| Wire Size (CMA) | .129 mm ² 26 AWG |

Industry Standards

| | |
|---------------------|-----------------------|
| Flammability Rating | Non-Plenum (CM Rated) |
|---------------------|-----------------------|

Operation/Application

| | |
|--------------|----|
| Halogen Free | No |
|--------------|----|

Other

| | |
|---------|--|
| Comment | North America has a corresponding part available under the TCPC-6ARFVB numbering scheme. |
|---------|--|

Packaging Features

| | |
|------------------|-----|
| Packaging Method | Bag |
|------------------|-----|

Product Availability

| | |
|--------|------|
| Region | Asia |
|--------|------|

Product Type Features

| | |
|--------------|------------|
| Product Type | Patch Cord |
|--------------|------------|

1933883-5

| | |
|-------------------------|-------------------|
| System | AMP NETCONNECT |
| Assembly Type | Plug to Plug |
| Connector Type (End A) | RJ45 Modular Plug |
| Connector Type (End B) | RJ45 Modular Plug |
| Performance Category | Category 6A |
| Cable Assembly Category | Industry Standard |
| Shielded | Yes |

Usage Conditions

| | |
|-----------------------------|---------------------------|
| Operating Temperature Range | -20 – 60 °C -4 – 140 °F |
| Storage Temperature | -20 – 80 °C -4 – 176 °F |

Regulatory Compliance/Certifications

| | |
|-----------------|-----------------------|
| Agency | Classification |
| RoHS 2011/65/EU | Compliant |