



2-1671000-8

Fiber Optic Panel, 1U, 19 in, partially loaded with 12 LC/UPC MM duplex adapters, black

Body Features

Chassis Color	Black
Finish	Powder coated

Configuration Features

Number of Ports	24
Front Connector Type	LC/UPC
Configuration	Adapters only
Number of Fibers	48
Port Style	Duplex

Dimensions

Height	44.450 mm 1.750 in
Width	482.600 mm 19.000 in

Packaging Features

Includes	Installation Instruction Mounting hardware
Packaging Method	Box/Carton
Packaging Quantity	1

Product Availability

Region	Asia EMEA
--------	-------------

Product Type Features

Product Type	Fiber Termination Panel
System	AMP NETCONNECT
Rack Units	1.0
Optical Mode	Multimode

Regulatory Compliance/Certifications

Agency
RoHS 2011/65/EU

Classification
Compliant