



2-2055578-6

MPOptimate® Trunk Cable, 24 fiber, duplex, OM4, 26 m, aqua

Body Features

Cable Color	Aqua
-------------	------

Configuration Features

Number of Fibers	24
Number of Connectors (End A)	2
Number of Connectors (End B)	2
Exit Angle to Exit Angle	180° to 180°

Dimensions

Assembly Length	26.00 m 85.30 ft
Cable Outer Diameter	.315 in 8 mm

Industry Standards

Flammability Rating	LSZH
---------------------	------

Product Availability

Region	Australia/New Zealand EMEA
--------	------------------------------

Product Type Features

Product Type	Trunk cable
System	AMP NETCONNECT MPOptimate®
Connector Type (End A)	MPO
Connector Type (End B)	MPO
Fiber Type	OM4
Fiber Diameter	50/125 µm
Optical Mode	Multimode
Polarity	Straight

Regulatory Compliance/Certifications

Agency	Classification
RoHS 2011/65/EU	Compliant

* Footnotes

Assembly Length	Assembly length includes the breakout lengths
-----------------	---